

Philips
DVD home theater system



HTS9810



Not a home cinema, but a cinema at home

with 9.1 Cinema Sound

Be submerged in grand sound, picture and design. Bask in 9.1 Cinema Sound - powered by Ambisound - which gives you the ultimate cinematic listening experience at home. HTS9810 is sheer beauty and top-performance for the movie connoisseur.

Connect

- EasyLink for easy control of connected devices via HDMI CEC
- Hi-Speed USB 2.0 Link plays media from USB flash drives
- MP3 Link plays music from portable media players

Hear

- 9.1 Cinema Sound for 9.1 surround sound from just 5 speakers
- Excellent sound quality with soft dome tweeters & DoubleBASS
- FullSound™ bringing CD listening experience to MP3

Live

- Wireless rear speakers for fewer wires across your room
- Touch screen controls for easy playback and volume control
- Full length tower speakers for more impressive sound

See

- Faroudja DCDi for incredibly sharp high quality video
- HDMI 1080p upscales to high definition for sharper pictures

PHILIPS
sense and simplicity

Specifications

Accessories

- **Included Accessories:** FM antenna, Interconnect cable, Quick start guide, Remote Control, Screws for wall mounting x2, User Manual, World Wide Warranty leaflet, Batteries for remote control, Full SCART cable, HDMI cable, MP3 Line-in cable, Power cord, Wall mounting bracket

Audio Playback

- **Compression format:** MP3, WMA
- **MP3 bit rates:** 32-256 kbps and VBR
- **Playback Media:** CD, CD-R, CD-R/RW, USB flash drive

Connectivity

- **Front / Side connections:** MP3 Line-in, USB
- **Rear Connections:** AUX in, Component Video output, Easy-Fit speaker connectors, HDMI output, Interconnect (to Power Box), SCART I (CVBS, RGB out), TV in (audio, cinch)
- **Subwoofer (Power Box):** AUX In (cinch, 2 pairs), Coaxial Digital input, FM Antenna, Interconnect (to Main Unit), Optical digital input

Dimensions

- **Packaging dimensions (W x H x D):** 800 x 732 x 1200 mm
- **Set dimensions (W x H x D):** 304.2 x 299.7 x 84.55 mm
- **Set weight:** 2.74 kg
- **Subwoofer dimensions (W x H x D):** 322 x 425 x 322 mm
- **Subwoofer Weight:** 12.7 kg

Loudspeakers

- **Center freq range:** 120Hz-20000 Hz
- **Center Speaker:** 2 way
- **Center speaker drivers:** 18mm Dome Tweeter, 2 x 2.5" woofers
- **Center speaker impedance:** 4 ohm
- **Satellite Speaker:** 2 way, 4 Floor standing pillars, Magnetically shielded front, Wireless rear speakers
- **Satellite speaker drivers:** 2x 3" full range woofer, 18mm Dome Tweeter, 2.5" Woofer
- **Satellite speaker freq range:** 120Hz-20000 Hz
- **Satellite speaker impedance:** 6 ohm
- **Subwoofer driver:** 1 x 6.5" Long Throw woofer
- **Subwoofer freq range:** 20-120 Hz
- **Subwoofer impedance:** 4 ohm
- **Subwoofer type:** Active

Picture/Display

- **D/A converter:** 12 bit, 108 MHz
- **Picture enhancement:** Video upscaling, Faroudja DCDi, High Def (720p, 1080i, 1080p)

Power

- **Power consumption:** 180 W

- **Power supply:** 220-240V, 50Hz
- **Standby power consumption:** < 1 W

Sound

- **D/A converter:** 24 bit, 192 kHz
- **Frequency response:** 20Hz-20000 Hz
- **Output power (RMS):** (@10%THD):8x75W (Front/Front Side/Rear/Rear Side)+1X100W(Center) + 1X100W(Subwoofer)
- **Signal to noise ratio:** >95 dB
- **Sound Enhancement:** Class "D" Digital Amplifier, Treble and Bass Control, ClearVoice, DoubleBass, Smart Surround
- **Equalizer settings:** Action, Classic, Concert, Drama, Jazz, Rock, Digital, Gaming, News, Party, Sports
- **Sound System:** Ambisound, Dolby Digital, Dolby Prologic II, DTS, Stereo

Still Picture Playback

- **Picture compression format:** JPEG
- **Picture enhancement:** Rotate, Slideshow with music playback, Zoom
- **Playback Media:** CD-R/RW, DVD+R/RW, USB flash drive

Tuner/Reception/Transmission

- **RDS:** Station Name
- **Tuner Bands:** AM, FM

Video Playback

- **Compression formats:** DivX 3.11, DivX 4.x, DivX 5.x, DivX 6.0, MPEG1, MPEG2, DivX Ultra, WMV 9
- **Playback Media:** CD-R/CD-RW, DVD-Video, Video CD/SVCD, DVD+R/RW, DVD-R/RW
- **Video disc playback system:** NTSC, PAL

Product dimensions

- **Product dimensions (W x H x D):** 30.42 x 29.97 x 8.455 cm
- **Weight:** 2.74 kg
- **Product dimensions with stand (W x H x D):** 30.42 x 30.594 x 13.52 cm
- **Weight (with stand):** 3.5 kg

Packaging dimensions

- **Packaging dimensions (W x H x D):** 80 x 73.2 x 120 cm
- **Gross weight:** 49 kg
- **Nett weight:** 42.634 kg
- **Tare weight:** 6.366 kg

Outer Carton

- **Outer carton (L x W x H):** 120 x 80 x 73.2 cm
- **Gross weight:** 49 kg
- **Nett weight:** 42.634 kg
- **Tare weight:** 6.366 kg

Product highlights

Faroudja DCDi

'Enjoy incredibly sharp, high quality video on your progressive scan TV with Faroudja DCDi. The feature alleviates jagged edges that appear when standard interlaced video is viewed, especially with moving images - thus delivering natural-looking action scenes. Bring your viewing experience to the next level with clearer smoother pictures.

9.1 Cinema Sound

9.1 Cinema Sound - powered by Ambisound - creates the ultimate all-around sound ambiance that modern cinemas provide. Without the clutter of a multitude of speakers, 9.1 Cinema Sound provides the incredible sense that there are speakers along the sides of the room. It recreates cinema sound right in your living room, delivering unparalleled surround sound that truly envelops you.

Wireless rear speakers

Wireless rear speakers give you scalability and mobility in speaker placement. Developed using interference-free technology, wireless speakers provide full surround sound without unsightly wire connections.

EasyLink

EasyLink lets you control multiple devices with one remote. It uses HDMI CEC industry-standard protocol to share functionality between devices through the HDMI cable. With one touch of a button, you can operate all your connected HDMI CEC enabled equipment simultaneously. Functions like standby and play can now be carried out with absolute ease.

Hi-Speed USB 2.0 Link

The Universal Serial Bus or USB is a protocol standard that is conveniently used to link PCs, peripherals and consumer electronic equipment. Hi-Speed USB devices have a data transfer rate of up to 480 Mbps - up from the 12 Mbps in original USB ones. With Hi-Speed USB 2.0 Link, all you have to do is plug in your USB device, select the movie, music or photo and play away.

MP3 Link

MP3 Link allows playback of MP3 files, directly from your portable media player, on your home theater system. Simply connect your portable MP3 player to the built-in MP3 Link jack and enjoy your MP3 music in the superior sound quality delivered by the Philips home theatre system. MP3 Link brings your portable music into the comfort of your living room.



Issue date 2008-08-30

Version: 1.0.5

12 NC: 8670 000 36321
EAN: 87 12581 38933 8

© 2008 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com